

edgeRX Gateway

CPU	MCIMX6Y2DVM05AA, ARM Cortex-A7,528MHz
Memory	512 MB DDR3 RAM, 4GB eMMC ROM
Ethernet	10/100M Ethernet
Wireless Communication	4G-LTE (Configurable) WiFi (Configurable) BLE 5.0
RS485	Modbus (optional)
LED	5 * Green LED including: System, BLE, RS485, Ethernet, 4G and WiFi
Button	Factory reset (long press > 5sec) BLE Pairing (short press)
USB	1 * USB 2.0 (optional)
Power Supply	Typical 12V DC input, range from 9V~36V Support PoE (IEEE 802.3af, 13W maximum) Configurable
Certification	FCC/ UL for North America CE for Europe SRRC for China TELEC for Japan
IP Rating	IP67
Mounting	Wall mounting DIN rail mounting
Operating Temperature	-40~85 degrees C
Dimension Weight	180.0mm x 150.0mm x 40.0mm

